



FAG

## ★ B71910-C-T-P4S-UL

Spindle bearing

Schaeffler ID:  
0191539880000

★ Preferred product

Spindle bearings B719..-C, adjusted,  
in pairs or sets, contact angle  $\alpha = 15^\circ$ ,  
restricted tolerances

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.
	0,127 kg	Weight

## Main Dimensions &amp; Performance Data

d	50 mm	Bore diameter
D	72 mm	Outside diameter
B	12 mm	Width
$C_r$	19.600 N	Basic dynamic load rating, radial
$C_{0r}$	11.900 N	Basic static load rating, radial
$C_{ur}$	1.260 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	19.000 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	30.000 1/min	Limiting speed for oil lubrication

## Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$r_{1 \min}$	0,6 mm	Minimum chamfer dimension
$\alpha$	15 °	Contact angle



### Mounting dimensions

$d_a$	55 mm	Diameter shaft shoulder
$d_a$	h12	Diameter shaft shoulder clearance
$D_a$	67,5 mm	Shoulder diameter outer ring
$D_a$	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,6 mm	Maximum recess radius
$r_{a1 \max}$	0,15 mm	Maximum recess radius
$E_{tk \min}$	56,8 mm	Minimum diameter injection pitch
$E_{tk \max}$	58,9 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	56,8 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	58,9 mm	Maximum diameter injection pitch
$a$	14,2 mm	Distance between the apexes of the pressure cones

### Additional information

$F_{VL}$	89 N	Preload force light
$F_{VM}$	313 N	Preload force medium
$F_{VH}$	642 N	Preload force heavy
$K_{aEL}$	274 N	Lift-off force light
$K_{aEM}$	1.044 N	Lift-off force medium
$K_{aEH}$	2.293 N	Lift-off force heavy
$c_{aL}$	45,6 N/ $\mu\text{m}$	Axial rigidity light
$c_{aM}$	80,2 N/ $\mu\text{m}$	Axial rigidity medium
$c_{aH}$	116 N/ $\mu\text{m}$	Axial rigidity heavy