

FAG



## ★ 2311-2RS-TVH

Self-aligning ball bearing

Schaeffler ID:  
0167074350000Self-aligning ball bearing 23...-2RS-TVH,  
seals, plastic cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.
	1,886 kg	Weight

## Main Dimensions &amp; Performance Data

d	55 mm	Bore diameter
D	120 mm	Outside diameter
B	43 mm	Width
$r_{\min}$	2 mm	Minimum chamfer dimension
$C_r$	52.000 N	Basic dynamic load rating, radial
$C_{0r}$	17.900 N	Basic static load rating, radial
$C_{ur}$	1.130 N	Fatigue load limit, radial
$n_G$	3.450 1/min	Limiting speed

## Dimensions

$D_2$	106,4 mm	Caliber diameter outer ring
$d_2$	70,5 mm	Caliber diameter inner ring

## Mounting dimensions

$d_{a \min}$	66 mm	Minimum diameter shaft shoulder
$D_{a \max}$	109 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2 mm	Maximum fillet radius

## Calculation factors

e	0,24	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y_1$	2,65	Dynamic axial load factor
$Y_2$	4,1	Dynamic axial load factor
$Y_0$	2,78	Static axial load factor