



FAG

## ★ B7030-C-T-P4S-UL

## Spindle bearing

Schaeffler ID:  
0191529900000

★ Preferred product

Spindle bearings B70...-C, adjusted, in pairs or sets, contact angle  $\alpha = 15^\circ$ , restricted tolerances

## Technical information



## Temperature range


$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.
	3,961 kg	Weight

## Main Dimensions &amp; Performance Data

d	150 mm	Bore diameter
D	225 mm	Outside diameter
B	35 mm	Width
$C_r$	187.000 N	Basic dynamic load rating, radial
$C_{0r}$	137.000 N	Basic static load rating, radial
$C_{ur}$	10.600 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	6.000 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	9.000 1/min	Limiting speed for oil lubrication

## Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$r_{1 \min}$	2,1 mm	Minimum chamfer dimension
$\alpha$	15 °	Contact angle



### Mounting dimensions

$d_a$	163 mm	Diameter shaft shoulder
$d_a$	h12	Diameter shaft shoulder clearance
$D_a$	213 mm	Shoulder diameter outer ring
$D_a$	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	2,1 mm	Maximum recess radius
$r_{a1 \max}$	1 mm	Maximum recess radius
$E_{tk \min}$	172,2 mm	Minimum diameter injection pitch
$E_{tk \max}$	181 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	172,2 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	181 mm	Maximum diameter injection pitch
$a$	42,6 mm	Distance between the apexes of the pressure cones

### Additional information

$F_{VL}$	1.104 N	Preload force light
$F_{VM}$	3.443 N	Preload force medium
$F_{VH}$	6.843 N	Preload force heavy
$K_{aEL}$	3.394 N	Lift-off force light
$K_{aEM}$	11.397 N	Lift-off force medium
$K_{aEH}$	24.140 N	Lift-off force heavy
$c_{aL}$	156 N/ $\mu$ m	Axial rigidity light
$c_{aM}$	260 N/ $\mu$ m	Axial rigidity medium
$c_{aH}$	367 N/ $\mu$ m	Axial rigidity heavy