

FAG

★ HS7010-C-T-P4S-UL



Angular contact ball bearing

Schaeffler ID:
0191841400000

★ Preferred product

Spindle bearings HS70...-C, adjusted,
in pairs or sets, contact angle $\alpha = 15^\circ$,
restricted tolerances

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.
	0,271 kg	Weight


Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	80 mm	Outside diameter
B	16 mm	Width
C_r	12.800 N	Basic dynamic load rating, radial
C_{0r}	8.200 N	Basic static load rating, radial
C_{ur}	860 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	24.000 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	38.000 1/min	Limiting speed for oil lubrication

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
$r_{1 \min}$	1 mm	Minimum chamfer dimension
α	15 °	Contact angle

Mounting dimensions



d_a	56 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	74 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,3 mm	Maximum recess radius
$E_{tk \min}$	61,7 mm	Minimum diameter injection pitch
$E_{tk \max}$	63 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	59,6 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	63 mm	Maximum diameter injection pitch
a	16,7 mm	Distance between the apexes of the pressure cones

Additional information

F_{VL}	45 N	Preload force light
F_{VM}	135 N	Preload force medium
F_{VH}	269 N	Preload force heavy
K_{aEL}	135 N	Lift-off force light
K_{aEM}	424 N	Lift-off force medium
K_{aEH}	884 N	Lift-off force heavy
c_{aL}	36,4 N/ μm	Axial rigidity light
c_{aM}	57,4 N/ μm	Axial rigidity medium
c_{aH}	78,8 N/ μm	Axial rigidity heavy