



FAG

## ★ B71909-E-T-P4S-UL

Spindle bearing

Schaeffler ID:  
0191539530000

Spindle bearing B719...-E-T-P4S, with steel balls

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.
	0,001 kg	Weight

## Main Dimensions &amp; Performance Data

d	45 mm	Bore diameter
D	68 mm	Outside diameter
B	12 mm	Width
$C_r$	18.200 N	Basic dynamic load rating, radial
$C_{0r}$	10.600 N	Basic static load rating, radial
$C_{ur}$	1.120 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	19.000 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	28.000 1/min	Limiting speed for oil lubrication

## Dimensions

$r_{\min}$	0,6 mm	Minimum chamfer dimension
$r_{1 \min}$	0,6 mm	Minimum chamfer dimension
$\alpha$	25 °	Contact angle



### Mounting dimensions

$d_a$	50 mm	Diameter shaft shoulder
$d_a$	h12	Diameter shaft shoulder clearance
$D_a$	63,5 mm	Shoulder diameter outer ring
$D_a$	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	0,6 mm	Maximum recess radius
$r_{a1 \max}$	0,15 mm	Maximum recess radius
$E_{tk \min}$	52,3 mm	Minimum diameter injection pitch
$E_{tk \max}$	54,5 mm	Maximum diameter injection pitch
$E_{tk1 \min}$	52,3 mm	Minimum diameter injection pitch
$E_{tk1 \max}$	54,5 mm	Maximum diameter injection pitch
$a$	19,2 mm	Distance between the apexes of the pressure cones

### Additional information

$F_{VL}$	116 N	Preload force light
$F_{VM}$	470 N	Preload force medium
$F_{VH}$	1.028 N	Preload force heavy
$K_{aEL}$	336 N	Lift-off force light
$K_{aEM}$	1.415 N	Lift-off force medium
$K_{aEH}$	3.203 N	Lift-off force heavy
$c_{aL}$	99 N/ $\mu\text{m}$	Axial rigidity light
$c_{aM}$	168 N/ $\mu\text{m}$	Axial rigidity medium
$c_{aH}$	232 N/ $\mu\text{m}$	Axial rigidity heavy