



FAG

★ N326-E-XL-M1


Cylindrical roller bearing

Schaeffler ID:
0192189150000

★ Preferred product

Cylindrical roller bearing N3..-E-M1, with cage, single row, non-locating bearing, 0 ribs on outer ring, 2 rib on inner ring, type N3

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	17,84 kg	Weight

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	280 mm	Outside diameter
B	58 mm	Width
C_r	720.000 N	Basic dynamic load rating, radial
C_{0r}	720.000 N	Basic static load rating, radial
C_{ur}	115.000 N	Fatigue load limit, radial
$n_{G \text{ Grease}}$	3.150 1/min	Limiting speed for grease lubrication
$n_{G \text{ Oil}}$	3.700 1/min	Limiting speed for oil lubrication

Dimensions

$r_{1 \min}$	4 mm	Minimum chamfer dimension
s_1	3,5 mm	Axial displacement
E	247 mm	Raceway diameter outer ring

Mounting dimensions

$d_{a \min}$	147 mm	Minimum diameter shaft shoulder
$D_{a \max}$	263 mm	Maximum diameter of housing shoulder
$r_{a1 \max}$	3 mm	Maximum recess radius