



FAG

★ NJ2204-E-XL-TVP2

Cylindrical roller bearing



Schaeffler ID:
0167346700000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	0,161 kg	Weight

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	47 mm	Outside diameter
B	18 mm	Width
C_r	38.500 N	Basic dynamic load rating, radial
C_{0r}	31.000 N	Basic static load rating, radial
C_{ur}	5.200 N	Fatigue load limit, radial
n_G	19.200 1/min	Limiting speed
$n_{\vartheta r}$	11.100 1/min	Reference speed

Dimensions

r_{min}	1 mm	Minimum chamfer dimension
$r_{1 min}$	0,6 mm	Minimum chamfer dimension
s	1,8 mm	Axial displacement
E	41,5 mm	Raceway diameter outer ring
F	26,5 mm	Raceway diameter inner ring
$D_{1 min}$	38,8 mm	Minimum rib diameter outer ring
d_1	29,7 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a min}$	24 mm	Minimum diameter shaft shoulder
$d_{a max}$	26 mm	Maximum diameter of shaft shoulder
$D_{a max}$	41 mm	Maximum diameter of housing shoulder
$d_{c min}$	32 mm	Minimum shaft shoulder
$r_{a max}$	1 mm	Maximum recess radius

Additional information

HJ2204-E

L-washer

