

FAG

## ★ NJ236-E-XL-M1

Cylindrical roller bearing



Schaeffler ID:  
0192273100000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-M1, with cage, single row, semi-locating bearing, 2 ribs on outer ring, 1 rib on inner ring, type NJ

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.
	18,66 kg	Weight

## Main Dimensions &amp; Performance Data

d	180 mm	Bore diameter
D	320 mm	Outside diameter
B	52 mm	Width
$C_r$	730.000 N	Basic dynamic load rating, radial
$C_{0r}$	830.000 N	Basic static load rating, radial
$C_{ur}$	124.000 N	Fatigue load limit, radial
$n_G$	3.250 1/min	Limiting speed
$n_{gr}$	1.850 1/min	Reference speed

## Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
$r_{1\min}$	4 mm	Minimum chamfer dimension
s	4,7 mm	Axial displacement
E	289 mm	Raceway diameter outer ring
F	217 mm	Raceway diameter inner ring
$D_{1\min}$	278,6 mm	Minimum rib diameter outer ring
$d_1$	230,2 mm	Maximum rib diameter inner ring

## Mounting dimensions

$d_{a\min}$	197 mm	Minimum diameter shaft shoulder
$d_{a\max}$	214 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	303 mm	Maximum diameter of housing shoulder
$d_{c\min}$	233 mm	Minimum shaft shoulder
$r_{a\max}$	3 mm	Maximum recess radius

Additional information

HJ236-E

L-washer

