

FAG



NJ2226-E-XL-TVP2

Cylindrical roller bearing

Schaeffler ID:
0167351610000Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information

**Temperature range**

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	10,5 kg	Weight

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	230 mm	Outside diameter
B	64 mm	Width
C_r	620.000 N	Basic dynamic load rating, radial
C_{0r}	730.000 N	Basic static load rating, radial
C_{ur}	120.000 N	Fatigue load limit, radial
n_G	3.500 1/min	Limiting speed
n_{gr}	2.280 1/min	Reference speed

Dimensions

r_{\min}	3 mm	Minimum chamfer dimension
$r_{1\min}$	3 mm	Minimum chamfer dimension
s	5,2 mm	Axial displacement
E	209,5 mm	Raceway diameter outer ring
F	153,5 mm	Raceway diameter inner ring
$D_{1\min}$	201,2 mm	Minimum rib diameter outer ring
d_1	164 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	144 mm	Minimum diameter shaft shoulder
$d_{a\max}$	151 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	216 mm	Maximum diameter of housing shoulder
$d_{c\min}$	168 mm	Minimum shaft shoulder
$r_{a\max}$	2,5 mm	Maximum recess radius

Additional information

HJ2226-E

L-washer

