

FAG

★ NJ2312-E-XL-TVP2

Cylindrical roller bearing

Schaeffler ID:
0192254900000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	2,79 kg	Weight

Main Dimensions & Performance Data



d	60 mm	Bore diameter
D	130 mm	Outside diameter
B	46 mm	Width
C_r	265.000 N	Basic dynamic load rating, radial
C_{0r}	260.000 N	Basic static load rating, radial
C_{ur}	50.000 N	Fatigue load limit, radial
n_G	6.500 1/min	Limiting speed
n_{gr}	4.250 1/min	Reference speed

Dimensions

r_{\min}	2,1 mm	Minimum chamfer dimension
$r_{1\min}$	2,1 mm	Minimum chamfer dimension
s	3,5 mm	Axial displacement
E	115 mm	Raceway diameter outer ring
F	77 mm	Raceway diameter inner ring
$D_{1\min}$	109,6 mm	Minimum rib diameter outer ring
d_1	84,4 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	72 mm	Minimum diameter shaft shoulder
$d_{a\max}$	75 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	118 mm	Maximum diameter of housing shoulder
$d_{c\min}$	86 mm	Minimum shaft shoulder
$r_{a\max}$	2,1 mm	Maximum recess radius



Additional information

HJ2312-E

L-washer

