



FAG

## ★ NJ2316-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:  
0192259030000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,  
with cage, single row, semi-locating  
bearing, 2 ribs on outer ring, 1 rib on inner  
ring, type NJ

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	5,863 kg	Weight

## Main Dimensions &amp; Performance Data

d	80 mm	Bore diameter
D	170 mm	Outside diameter
B	58 mm	Width
$C_r$	420.000 N	Basic dynamic load rating, radial
$C_{0r}$	425.000 N	Basic static load rating, radial
$C_{ur}$	79.000 N	Fatigue load limit, radial
$n_G$	4.800 1/min	Limiting speed
$n_{gr}$	3.450 1/min	Reference speed

## Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$r_{1\min}$	2,1 mm	Minimum chamfer dimension
s	3,7 mm	Axial displacement
E	151 mm	Raceway diameter outer ring
F	101 mm	Raceway diameter inner ring
$D_{1\min}$	143,9 mm	Minimum rib diameter outer ring
$d_1$	110,4 mm	Maximum rib diameter inner ring

## Mounting dimensions

$d_{a\min}$	92 mm	Minimum diameter shaft shoulder
$d_{a\max}$	99 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	158 mm	Maximum diameter of housing shoulder
$d_{c\min}$	114 mm	Minimum shaft shoulder
$r_{a\max}$	2,1 mm	Maximum recess radius

Additional information

HJ2316-E

L-washer

