

FAG

NJ2319-E-XL-TVP2

Cylindrical roller bearing

Schaeffler ID:
0192262920000Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	9,355 kg	Weight

Main Dimensions & Performance Data



d	95 mm	Bore diameter
D	200 mm	Outside diameter
B	67 mm	Width
C_r	540.000 N	Basic dynamic load rating, radial
C_{0r}	580.000 N	Basic static load rating, radial
C_{ur}	101.000 N	Fatigue load limit, radial
n_G	4.050 1/min	Limiting speed
$n_{\vartheta r}$	2.800 1/min	Reference speed

Dimensions

r_{\min}	3 mm	Minimum chamfer dimension
$r_{1\min}$	3 mm	Minimum chamfer dimension
s	5,6 mm	Axial displacement
E	177,5 mm	Raceway diameter outer ring
F	121,5 mm	Raceway diameter inner ring
$D_{1\min}$	169,6 mm	Minimum rib diameter outer ring
d_1	132 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	109 mm	Minimum diameter shaft shoulder
$d_{a\max}$	119 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	186 mm	Maximum diameter of housing shoulder
$d_{c\min}$	134 mm	Minimum shaft shoulder
$r_{a\max}$	2,5 mm	Maximum recess radius



Additional information

HJ2319-E

L-washer

