

FAG

★ NJ2304-E-XL-TVP2

Cylindrical roller bearing



Schaeffler ID:
0167353070000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,212 kg	Weight

Main Dimensions & Performance Data

d	20 mm	Bore diameter
D	52 mm	Outside diameter
B	21 mm	Width
C_r	49.500 N	Basic dynamic load rating, radial
C_{0r}	39.000 N	Basic static load rating, radial
C_{ur}	6.300 N	Fatigue load limit, radial
n_G	17.200 1/min	Limiting speed
n_{gr}	9.700 1/min	Reference speed

Dimensions

r_{\min}	1,1 mm	Minimum chamfer dimension
$r_{1\min}$	0,6 mm	Minimum chamfer dimension
s	1,9 mm	Axial displacement
E	45,5 mm	Raceway diameter outer ring
F	27,5 mm	Raceway diameter inner ring
$D_{1\min}$	42,4 mm	Minimum rib diameter outer ring
d_1	31,3 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	24 mm	Minimum diameter shaft shoulder
$d_{a\max}$	27 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	45 mm	Maximum diameter of housing shoulder
$d_{c\min}$	33 mm	Minimum shaft shoulder
$r_{a\max}$	1 mm	Maximum recess radius

Additional information

HJ2304-E

L-washer

