



FAG

## NJ2326-E-XL-M1



Cylindrical roller bearing

Schaeffler ID:  
0192267210000

Cylindrical roller bearing NJ..-E-XL-M1, with cage, single row, semi-locating bearing, 2 ribs on outer ring, 1 rib on inner ring, type NJ

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.
	29,4 kg	Weight

## Main Dimensions &amp; Performance Data

d	130 mm	Bore diameter
D	280 mm	Outside diameter
B	93 mm	Width
$C_r$	1.080.000 N	Basic dynamic load rating, radial
$C_{0r}$	1.220.000 N	Basic static load rating, radial
$C_{ur}$	198.000 N	Fatigue load limit, radial
$n_G$	3.700 1/min	Limiting speed
$n_{gr}$	1.750 1/min	Reference speed

## Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
$r_{1\min}$	4 mm	Minimum chamfer dimension
s	8,1 mm	Axial displacement
E	247 mm	Raceway diameter outer ring
F	167 mm	Raceway diameter inner ring
$D_{1\min}$	235,2 mm	Minimum rib diameter outer ring
$d_1$	181,7 mm	Maximum rib diameter inner ring

## Mounting dimensions

$d_{a\min}$	147 mm	Minimum diameter shaft shoulder
$d_{a\max}$	164 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	263 mm	Maximum diameter of housing shoulder
$d_{c\min}$	184 mm	Minimum shaft shoulder
$r_{a\max}$	3 mm	Maximum recess radius

Additional information

HJ2326-E

L-washer

