



FAG

★ NJ317-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167365910000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	4,61 kg	Weight

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	180 mm	Outside diameter
B	41 mm	Width
C_r	320.000 N	Basic dynamic load rating, radial
C_{0r}	300.000 N	Basic static load rating, radial
C_{ur}	54.000 N	Fatigue load limit, radial
n_G	4.550 1/min	Limiting speed
n_{gr}	3.900 1/min	Reference speed

Dimensions

r_{\min}	3 mm	Minimum chamfer dimension
$r_{1\min}$	3 mm	Minimum chamfer dimension
s	1,3 mm	Axial displacement
E	160 mm	Raceway diameter outer ring
F	108 mm	Raceway diameter inner ring
$D_{1\min}$	152,7 mm	Minimum rib diameter outer ring
d_1	117,8 mm	Maximum rib diameter inner ring

Mounting dimensions

$d_{a\min}$	99 mm	Minimum diameter shaft shoulder
$d_{a\max}$	106 mm	Maximum diameter of shaft shoulder
$D_{a\max}$	166 mm	Maximum diameter of housing shoulder
$d_{c\min}$	119 mm	Minimum shaft shoulder
$r_{a\max}$	2,5 mm	Maximum recess radius

Additional information

HJ317-E

L-washer

