



FAG

★ NJ324-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0190045590000

★ Preferred product

Cylindrical roller bearing NJ..-E-XL-TVP2,
with cage, single row, semi-locating
bearing, 2 ribs on outer ring, 1 rib on inner
ring, type NJ

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	13,5 kg	Weight

Main Dimensions & Performance Data

d	120 mm	Bore diameter
D	260 mm	Outside diameter
B	55 mm	Width
C_r	610.000 N	Basic dynamic load rating, radial
C_{0r}	600.000 N	Basic static load rating, radial
C_{ur}	97.000 N	Fatigue load limit, radial
n_G	3.050 1/min	Limiting speed
n_{gr}	2.650 1/min	Reference speed

Dimensions

r_{min}	3 mm	Minimum chamfer dimension
r_{1min}	3 mm	Minimum chamfer dimension
s	3,5 mm	Axial displacement
E	230 mm	Raceway diameter outer ring
F	154 mm	Raceway diameter inner ring
D_{1min}	218,7 mm	Minimum rib diameter outer ring
d_1	168,1 mm	Maximum rib diameter inner ring

Mounting dimensions

d_{amin}	134 mm	Minimum diameter shaft shoulder
d_{amax}	151 mm	Maximum diameter of shaft shoulder
D_{amax}	246 mm	Maximum diameter of housing shoulder
d_{cmin}	171 mm	Minimum shaft shoulder
r_{amax}	2,5 mm	Maximum recess radius

Additional information

HJ324-E

L-washer

