

FAG

★ NU1034-XL-M1

Cylindrical roller bearing



Schaeffler ID:
0167373260000

★ Preferred product

Cylindrical roller bearing NU..-XL-M1, with cage, single row, non-locating bearing, 2 ribs on outer ring, 0 ribs on inner ring (smooth), type NU

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	7,86 kg	Weight

Main Dimensions & Performance Data

d	170 mm	Bore diameter
D	260 mm	Outside diameter
B	42 mm	Width
C_r	350.000 N	Basic dynamic load rating, radial
C_{0r}	435.000 N	Basic static load rating, radial
C_{ur}	52.000 N	Fatigue load limit, radial
n_G	4.300 1/min	Limiting speed
n_{gr}	2.750 1/min	Reference speed

Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
$r_{1 min}$	2,1 mm	Minimum chamfer dimension
s	4,8 mm	Axial displacement
E	237 mm	Raceway diameter outer ring
F	193 mm	Raceway diameter inner ring
$D_{1 min}$	229,1 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a min}$	180 mm	Minimum diameter shaft shoulder
$d_{a max}$	190 mm	Maximum diameter of shaft shoulder
$d_{b min}$	197 mm	Minimum shaft shoulder
$D_{a max}$	250 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,1 mm	Maximum recess radius
$r_{a1 max}$	2,1 mm	Maximum recess radius

