



FAG

★ NU226-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167389180000

★ Preferred product

Cylindrical roller bearing NU...-E-XL-TVP2,
with cage, single row, non-locating bearing,
2 ribs on outer ring, 0 ribs on inner ring
(smooth), type NU

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	6,4 kg	Weight

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	230 mm	Outside diameter
B	40 mm	Width
C_r	425.000 N	Basic dynamic load rating, radial
C_{0r}	445.000 N	Basic static load rating, radial
C_{ur}	56.000 N	Fatigue load limit, radial
n_G	3.500 1/min	Limiting speed
$n_{\vartheta r}$	2.800 1/min	Reference speed

Dimensions

r_{min}	3 mm	Minimum chamfer dimension
$r_{1 min}$	3 mm	Minimum chamfer dimension
s	1,2 mm	Axial displacement
E	209,5 mm	Raceway diameter outer ring
F	153,5 mm	Raceway diameter inner ring
$D_{1 min}$	201,2 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a min}$	144 mm	Minimum diameter shaft shoulder
$d_{a max}$	151 mm	Maximum diameter of shaft shoulder
$d_{b min}$	158 mm	Minimum shaft shoulder
$D_{a max}$	216 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,5 mm	Maximum recess radius
$r_{a1 max}$	2,5 mm	Maximum recess radius

