



FAG

★ NU216-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167379890000

★ Preferred product

Cylindrical roller bearing NU...-E-XL-TVP2,
with cage, single row, non-locating bearing,
2 ribs on outer ring, 0 ribs on inner ring
(smooth), type NU

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	1,51 kg	Weight

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	140 mm	Outside diameter
B	26 mm	Width
C_r	166.000 N	Basic dynamic load rating, radial
C_{0r}	168.000 N	Basic static load rating, radial
C_{ur}	23.100 N	Fatigue load limit, radial
n_G	6.100 1/min	Limiting speed
n_{gr}	4.200 1/min	Reference speed

Dimensions

r_{min}	2 mm	Minimum chamfer dimension
$r_{1 min}$	2 mm	Minimum chamfer dimension
s	1,3 mm	Axial displacement
E	127,3 mm	Raceway diameter outer ring
F	95,3 mm	Raceway diameter inner ring
$D_{1 min}$	122,9 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a min}$	91 mm	Minimum diameter shaft shoulder
$d_{a max}$	94 mm	Maximum diameter of shaft shoulder
$d_{b min}$	97 mm	Minimum shaft shoulder
$D_{a max}$	129 mm	Maximum diameter of housing shoulder
$r_{a max}$	2 mm	Maximum recess radius
$r_{a1 max}$	2 mm	Maximum recess radius

