

FAG



NU2330-E-XL-M1

Cylindrical roller bearing

Schaeffler ID:
0192455720000Cylindrical roller bearing NU..-E-XL-M1,
with cage, single row, non-locating bearing,
2 ribs on outer ring, 0 ribs on inner ring
(smooth), type NU

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	150 °C	Operating temperature max.
	42,44 kg	Weight

Main Dimensions & Performance Data

d	150 mm	Bore diameter
D	320 mm	Outside diameter
B	108 mm	Width
C_r	1.380.000 N	Basic dynamic load rating, radial
C_{0r}	1.600.000 N	Basic static load rating, radial
C_{ur}	250.000 N	Fatigue load limit, radial
n_G	3.200 1/min	Limiting speed
n_{gr}	1.460 1/min	Reference speed

Dimensions

r_{\min}	4 mm	Minimum chamfer dimension
$r_{1\min}$	4 mm	Minimum chamfer dimension
s	9,7 mm	Axial displacement
E	283 mm	Raceway diameter outer ring
F	193 mm	Raceway diameter inner ring
$D_{1\min}$	269,8 mm	Minimum rib diameter outer ring

Mounting dimensions

$d_{a\min}$	167 mm	Minimum diameter shaft shoulder
$d_{a\max}$	190 mm	Maximum diameter of shaft shoulder
$d_{b\min}$	195 mm	Minimum shaft shoulder
$D_{a\max}$	303 mm	Maximum diameter of housing shoulder
$r_{a\max}$	3 mm	Maximum recess radius
$r_{a1\max}$	3 mm	Maximum recess radius

