



FAG

★ NUP303-E-XL-TVP2

Cylindrical roller bearing

Schaeffler ID:
0192546520000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,142 kg	Weight

Main Dimensions & Performance Data

d	17 mm	Bore diameter
D	47 mm	Outside diameter
B	14 mm	Width
C_r	30.000 N	Basic dynamic load rating, radial
C_{0r}	21.200 N	Basic static load rating, radial
C_{ur}	3.400 N	Fatigue load limit, radial
n_G	19.600 1/min	Limiting speed
n_{gr}	13.500 1/min	Reference speed

Dimensions

r_{\min}	1 mm	Minimum chamfer dimension
$r_{1\min}$	0,6 mm	Minimum chamfer dimension
E	40,2 mm	Raceway diameter outer ring
F	24,2 mm	Raceway diameter inner ring
B_3	2,5 mm	Width of loose rib

Mounting dimensions

d_1	27,6 mm	Maximum rib diameter inner ring
$D_{1\min}$	37,1 mm	Minimum rib diameter outer ring
$d_{a\min}$	21,2 mm	Minimum diameter shaft shoulder
$d_{c\min}$	28 mm	Minimum shaft shoulder
$D_{a\max}$	42,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	1 mm	Maximum recess radius

