

FAG

★ NUP320-E-XL-TVP2

Cylindrical roller bearing




Schaeffler ID:
0167416250000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	7,74 kg	Weight

Main Dimensions & Performance Data

d	100 mm	Bore diameter
D	215 mm	Outside diameter
B	47 mm	Width
C_r	450.000 N	Basic dynamic load rating, radial
C_{0r}	425.000 N	Basic static load rating, radial
C_{ur}	72.000 N	Fatigue load limit, radial
n_G	3.700 1/min	Limiting speed
n_{gr}	3.350 1/min	Reference speed

Dimensions

r_{\min}	3 mm	Minimum chamfer dimension
$r_{1\min}$	3 mm	Minimum chamfer dimension
E	191,5 mm	Raceway diameter outer ring
F	127,5 mm	Raceway diameter inner ring
B_3	7,5 mm	Width of loose rib

Mounting dimensions

d_1	139,4 mm	Maximum rib diameter inner ring
$D_{1\min}$	182 mm	Minimum rib diameter outer ring
$d_{a\min}$	114 mm	Minimum diameter shaft shoulder
$d_{c\min}$	143 mm	Minimum shaft shoulder
$D_{a\max}$	201 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,5 mm	Maximum recess radius