

FAG

★ NUP2210-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167409550000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	0,583 kg	Weight

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	90 mm	Outside diameter
B	23 mm	Width
C_r	92.000 N	Basic dynamic load rating, radial
C_{0r}	88.000 N	Basic static load rating, radial
C_{ur}	15.300 N	Fatigue load limit, radial
n_G	9.700 1/min	Limiting speed
n_{gr}	5.300 1/min	Reference speed

Dimensions

r_{min}	1,1 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
E	81,5 mm	Raceway diameter outer ring
F	59,5 mm	Raceway diameter inner ring
B_3	4 mm	Width of loose rib

Mounting dimensions

d_1	64 mm	Maximum rib diameter inner ring
$D_{1 min}$	78,3 mm	Minimum rib diameter outer ring
$d_{a min}$	57 mm	Minimum diameter shaft shoulder
$d_{c min}$	67 mm	Minimum shaft shoulder
$D_{a max}$	83 mm	Maximum diameter of housing shoulder
$r_{a max}$	1 mm	Maximum recess radius