

FAG

★ NUP2219-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:
0167410480000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	3,753 kg	Weight

Main Dimensions & Performance Data

d	95 mm	Bore diameter
D	170 mm	Outside diameter
B	43 mm	Width
C_r	340.000 N	Basic dynamic load rating, radial
C_{0r}	370.000 N	Basic static load rating, radial
C_{ur}	65.000 N	Fatigue load limit, radial
n_G	4.850 1/min	Limiting speed
n_{gr}	3.050 1/min	Reference speed

Dimensions

r_{\min}	2,1 mm	Minimum chamfer dimension
$r_{1\min}$	2,1 mm	Minimum chamfer dimension
E	154,5 mm	Raceway diameter outer ring
F	112,5 mm	Raceway diameter inner ring
B_3	6,5 mm	Width of loose rib

Mounting dimensions

d_1	120,5 mm	Maximum rib diameter inner ring
$D_{1\min}$	148,6 mm	Minimum rib diameter outer ring
$d_{a\min}$	107 mm	Minimum diameter shaft shoulder
$d_{c\min}$	123 mm	Minimum shaft shoulder
$D_{a\max}$	158 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,1 mm	Maximum recess radius

