



FAG

★ 22224-E1-XL

Spherical roller bearing

Schaeffler ID:
0167044280000Spherical roller bearings 222...-E1, main
dimensions to DIN 635-2

★ Preferred product

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.
	8,858 kg	Weight

Main Dimensions & Performance Data

d	120 mm	Bore diameter
D	215 mm	Outside diameter
B	58 mm	Width
C_r	640.000 N	Basic dynamic load rating, radial
C_{0r}	740.000 N	Basic static load rating, radial
C_{ur}	73.000 N	Fatigue load limit, radial
n_G	3.650 1/min	Limiting speed
n_{gr}	2.700 1/min	Reference speed

Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	192 mm	Bore diameter outer ring
d_2	141,9 mm	Raceway diameter of the inner ring
d_s	6,3 mm	Diameter lubrication hole
n_s	12,2 mm	Width of lubricating groove

Mounting dimensions

$d_{a min}$	132 mm	Minimum diameter shaft shoulder
$D_{a max}$	203 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,1 mm	Maximum recess radius

Additional information

e	0,25	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,71	Dynamic axial load factor
Y ₂	4,04	Dynamic axial load factor
Y ₀	2,65	Static axial load factor