

FAG




## NUP2228-E-XL-M1

Cylindrical roller bearing

Schaeffler ID:  
0192534430000Cylindrical roller bearing NUP.-E-XL-M1,  
with cage, single row, locating bearing, 2  
ribs on outer ring, 1 rib on inner ring, rib  
washer internal, type NUP

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.
	15,1 kg	Weight

## Main Dimensions &amp; Performance Data

d	140 mm	Bore diameter
D	250 mm	Outside diameter
B	68 mm	Width
$C_r$	670.000 N	Basic dynamic load rating, radial
$C_{0r}$	830.000 N	Basic static load rating, radial
$C_{ur}$	133.000 N	Fatigue load limit, radial
$n_G$	4.250 1/min	Limiting speed
$n_{gr}$	2.050 1/min	Reference speed

## Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
$r_{1\min}$	3 mm	Minimum chamfer dimension
E	225 mm	Raceway diameter outer ring
F	169 mm	Raceway diameter inner ring
$B_3$	12 mm	Width of loose rib

## Mounting dimensions

$d_1$	179,4 mm	Maximum rib diameter inner ring
$D_{1\min}$	216,7 mm	Minimum rib diameter outer ring
$d_{a\min}$	154 mm	Minimum diameter shaft shoulder
$d_{c\min}$	182 mm	Minimum shaft shoulder
$D_{a\max}$	236 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,5 mm	Maximum recess radius