

FAG

## ★ NUP2313-E-XL-TVP2

Cylindrical roller bearing


Schaeffler ID:  
0167412850000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.
	3,4 kg	Weight

## Main Dimensions &amp; Performance Data

d	65 mm	Bore diameter
D	140 mm	Outside diameter
B	48 mm	Width
$C_r$	295.000 N	Basic dynamic load rating, radial
$C_{0r}$	285.000 N	Basic static load rating, radial
$C_{ur}$	54.000 N	Fatigue load limit, radial
$n_G$	5.900 1/min	Limiting speed
$n_{gr}$	4.000 1/min	Reference speed

## Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$r_{1\min}$	2,1 mm	Minimum chamfer dimension
E	124,5 mm	Raceway diameter outer ring
F	82,5 mm	Raceway diameter inner ring
$B_3$	8 mm	Width of loose rib

## Mounting dimensions

$d_1$	90,5 mm	Maximum rib diameter inner ring
$D_{1\min}$	118,6 mm	Minimum rib diameter outer ring
$d_{a\min}$	77 mm	Minimum diameter shaft shoulder
$d_{c\min}$	93 mm	Minimum shaft shoulder
$D_{a\max}$	128 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,1 mm	Maximum recess radius

