

FAG

★ NUP2316-E-XL-TVP2

Cylindrical roller bearing




Schaeffler ID:
0167413230000

★ Preferred product

Cylindrical roller bearing NUP.-E-XL-TVP2, with cage, single row, locating bearing, 2 ribs on outer ring, 1 rib on inner ring, rib washer internal, type NUP

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.
	6 kg	Weight

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	170 mm	Outside diameter
B	58 mm	Width
C_r	420.000 N	Basic dynamic load rating, radial
C_{0r}	425.000 N	Basic static load rating, radial
C_{ur}	79.000 N	Fatigue load limit, radial
n_G	4.800 1/min	Limiting speed
n_{gr}	3.450 1/min	Reference speed

Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
$r_{1 min}$	2,1 mm	Minimum chamfer dimension
E	151 mm	Raceway diameter outer ring
F	101 mm	Raceway diameter inner ring
B_3	9 mm	Width of loose rib

Mounting dimensions

d_1	110,4 mm	Maximum rib diameter inner ring
$D_{1 min}$	143,9 mm	Minimum rib diameter outer ring
$d_{a min}$	92 mm	Minimum diameter shaft shoulder
$d_{c min}$	114 mm	Minimum shaft shoulder
$D_{a max}$	158 mm	Maximum diameter of housing shoulder
$r_{a max}$	2,1 mm	Maximum recess radius