

★ 21310-E1-XL-K



Spherical roller bearing

Schaeffler ID:
0219425440000

★ Preferred product

Spherical roller bearings 213...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	200 °C	Operating temperature max.
	1,29 kg	Weight

Main Dimensions & Performance Data

d	50 mm	Bore diameter
D	110 mm	Outside diameter
B	27 mm	Width
C_r	129.000 N	Basic dynamic load rating, radial
C_{0r}	130.000 N	Basic static load rating, radial
C_{ur}	17.700 N	Fatigue load limit, radial
n_G	9.000 1/min	Limiting speed
n_{gr}	5.400 1/min	Reference speed

Dimensions

r_{\min}	2 mm	Minimum chamfer dimension
D_1	89,8 mm	Bore diameter outer ring
d_2	67,7 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	4,8 mm	Width of lubricating groove

Mounting dimensions

$d_{a \min}$	61 mm	Minimum diameter shaft shoulder
$d_{a \max}$	67 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	99 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2 mm	Maximum recess radius
$d_{b \min}$	55 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve

Additional information

e	0,21	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H310	Adapter sleeve
Y ₁	3,17	Dynamic axial load factor
	AHX310	Withdrawal sleeve
Y ₂	4,72	Dynamic axial load factor
Y ₀	3,1	Static axial load factor