


## Technical information



### Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	200 °C	Operating temperature max.
	1,6 kg	Weight

### Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	125 mm	Outside diameter
B	31 mm	Width
$C_r$	211.000 N	Basic dynamic load rating, radial
$C_{0r}$	226.000 N	Basic static load rating, radial
$C_{ur}$	28.500 N	Fatigue load limit, radial
$n_G$	6.700 1/min	Limiting speed
$n_{gr}$	3.950 1/min	Reference speed

### Dimensions

$r_{min}$	1,5 mm	Minimum chamfer dimension
$D_1$	112,5 mm	Bore diameter outer ring
$d_2$	84,4 mm	Raceway diameter of the inner ring
$d_s$	3,2 mm	Diameter lubrication hole
$n_s$	6,5 mm	Width of lubricating groove

### Mounting dimensions

$d_{a min}$	79 mm	Minimum diameter shaft shoulder
$D_{a max}$	116 mm	Maximum diameter of housing shoulder
$r_{a max}$	1,5 mm	Maximum recess radius

**Additional information**

e	0,23	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y <sub>1</sub>	2,95	Dynamic axial load factor
Y <sub>2</sub>	4,4	Dynamic axial load factor
Y <sub>0</sub>	2,89	Static axial load factor