

FAG

★ 22234-E1-XL

Spherical roller bearing


Schaeffler ID:
0190182400000

★ Preferred product

X-life

Spherical roller bearings 222...-E1, main dimensions to DIN 635-2

Technical information



Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.
	27,445 kg	Weight

Main Dimensions & Performance Data

d	170 mm	Bore diameter
D	310 mm	Outside diameter
B	86 mm	Width
C _r	1.320.000 N	Basic dynamic load rating, radial
C _{0r}	1.570.000 N	Basic static load rating, radial
C _{ur}	144.000 N	Fatigue load limit, radial
n _G	2.550 1/min	Limiting speed
n _{gr}	1.780 1/min	Reference speed

Dimensions

r _{min}	4 mm	Minimum chamfer dimension
D ₁	275,4 mm	Bore diameter outer ring
d ₂	199,8 mm	Raceway diameter of the inner ring
d _s	9,5 mm	Diameter lubrication hole
n _s	17,7 mm	Width of lubricating groove

Mounting dimensions

d _{a min}	187 mm	Minimum diameter shaft shoulder
D _{a max}	293 mm	Maximum diameter of housing shoulder
r _{a max}	3 mm	Maximum recess radius

Additional information		
e	0,26	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,6	Dynamic axial load factor
Y ₂	3,87	Dynamic axial load factor
Y ₀	2,54	Static axial load factor