

FAG

## ★ 23022-E1-XL-TVPB


Spherical roller bearing

Schaeffler ID:  
0190010100000Spherical roller bearings 230...-E1, main  
dimensions to DIN 635-2

★ Preferred product

X-life

## Technical information



## Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	120 °C	Operating temperature max.
	3,505 kg	Weight

## Main Dimensions &amp; Performance Data

d	110 mm	Bore diameter
D	170 mm	Outside diameter
B	45 mm	Width
$C_r$	400.000 N	Basic dynamic load rating, radial
$C_{0r}$	530.000 N	Basic static load rating, radial
$C_{ur}$	54.000 N	Fatigue load limit, radial
$n_G$	4.200 1/min	Limiting speed
$n_{gr}$	3.000 1/min	Reference speed

## Dimensions

$r_{min}$	2 mm	Minimum chamfer dimension
$D_1$	154,6 mm	Bore diameter outer ring
$d_2$	123,7 mm	Raceway diameter of the inner ring
$d_s$	3,2 mm	Diameter lubrication hole
$n_s$	6,5 mm	Width of lubricating groove

## Mounting dimensions

$d_{a min}$	118,8 mm	Minimum diameter shaft shoulder
$D_{a max}$	161,2 mm	Maximum diameter of housing shoulder
$r_{a max}$	2 mm	Maximum recess radius

**Additional information**

e	0,23	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y <sub>1</sub>	2,9	Dynamic axial load factor
Y <sub>2</sub>	4,31	Dynamic axial load factor
Y <sub>0</sub>	2,83	Static axial load factor