



Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	18,349 kg	Weight

Main Dimensions & Performance Data

d	160 mm	Bore diameter
D	270 mm	Outside diameter
B	86 mm	Width
C_r	1.160.000 N	Basic dynamic load rating, radial
C_{0r}	1.550.000 N	Basic static load rating, radial
C_{ur}	166.000 N	Fatigue load limit, radial
n_G	2.490 1/min	Limiting speed
n_{gr}	1.560 1/min	Reference speed

Dimensions

r_{\min}	2,1 mm	Minimum chamfer dimension
D_1	238,3 mm	Bore diameter outer ring
d_2	183,2 mm	Raceway diameter of the inner ring
d_s	8 mm	Diameter lubrication hole
n_s	15 mm	Width of lubricating groove

Mounting dimensions

$d_{a \min}$	172 mm	Minimum diameter shaft shoulder
$D_{a \max}$	258 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius
$B_{a \min}$	8 mm	Minimum cavity width of the sleeve
$d_{a \max}$	183 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	170 mm	Minimum cavity diameter of the sleeve

Additional information

	H3132	Adapter sleeve
e	0,29	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,32	Dynamic axial load factor
	AH3132A	Withdrawal sleeve
Y ₂	3,45	Dynamic axial load factor
Y ₀	2,26	Static axial load factor