


FAG

32934

Tapered roller bearing

Schaeffler ID:
0167132650000Tapered roller bearings 329, main
dimensions to DIN ISO 355 / DIN 720,
separable, adjusted or in pairs

Technical information



Main Dimensions & Performance Data

d	170 mm	Bore diameter
D	230 mm	Outside diameter
B	38 mm	Width, inner ring
C	30 mm	Width, outer ring
T	38 mm	Width, total
C_r	295.000 N	Basic dynamic load rating, radial
C_{0r}	560.000 N	Basic static load rating, radial
C_{ur}	60.000 N	Fatigue load limit, radial
n_G	2.850 1/min	Limiting speed
n_{gr}	1.790 1/min	Thermal speed rating
	4,32 kg	Weight

Dimensions

	T3DC170	Comparative designation to ISO 10317 and ISO 355
$r_{1,2 \text{ min}}$	2,5 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \text{ min}}$	2 mm	Minimum chamfer dimension of outer ring back face
a	42 mm	Distance between the apexes of the pressure cones
d_1	199 mm	Guidance rib diameter of inner ring

Mounting dimensions

$d_{a \max}$	183 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	180 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	213 mm	Minimum diameter of housing shoulder
$D_{a \max}$	220 mm	Maximum diameter of housing shoulder
$D_{b \min}$	222 mm	Minimum diameter of housing shoulder
$C_{a \min}$	7 mm	Minimum axial space
$C_{b \min}$	8 mm	Minimum axial space
$r_{a \max}$	2,5 mm	Maximum fillet radius of shaft
$r_{b \max}$	2 mm	Maximum fillet radius of housing

Calculation factors

e	0,38	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,57	Dynamic axial load factor
Y_0	0,86	Static axial load factor

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	200 °C	Operating temperature max.