



## GE10-UK

### Spherical plain bearing

Schaeffler ID:  
0066497340000

Radial spherical plain bearing, maintenance-free, sliding layer: PTFE composite, inner ring curved surface with hard chromium coating, DIN ISO 12240-1, dimension series E, open design

#### Technical information

#### Main Dimensions & Performance Data

D	19 mm	Outside diameter bearing
d	10 mm	Bore diameter bearing
B	9 mm	Width Inner ring
C	6 mm	Width Outer ring
$C_r$	8.640 N	Basic dynamic load rating, radial
$C_{0r}$	21.600 N	Basic static load rating, radial
	10,76 g	Weight

#### Dimensions

$d_K$	16 mm	Ball diameter
$\alpha$	12 °	Tilt angle
$G_r$	0 - 0,032 mm	Radial Clearance
$d_{OT}$	0 mm	Bore diameter bearing, upper tolerance
$d_{UT}$	-0,008 mm	Bore diameter bearing, lower tolerance
$D_{OT}$	0 mm	Outside diameter, upper tolerance
$D_{UT}$	-0,009 mm	Outside diameter, lower tolerance
$B_{OT}$	0 mm	Width inner ring, upper tolerance
$B_{UT}$	-0,12 mm	Width inner ring, lower tolerance
$C_{OT}$	0 mm	Width outer ring, upper tolerance
$C_{UT}$	-0,24 mm	Width outer ring, lower tolerance

#### Mounting dimensions

$r_{1smin}$	0,3 mm	Edge Spacing
$r_{2smin}$	0,3 mm	Edge Spacing
$d_{amax}$	13,2 mm	Connection measure Inner ring
$D_{amin}$	15,5 mm	Housing Connection Diameter

#### Temperature range

$T_{min}$	-50 °C	Operating temperature min.
$T_{max}$	200 °C	Operating temperature max.

