



FAG

32940-A

Tapered roller bearing

Schaeffler ID:
0190568500000Tapered roller bearings 329, main
dimensions to DIN ISO 355 / DIN 720,
separable, adjusted or in pairs

Technical information

**Main Dimensions & Performance Data**

d	200 mm	Bore diameter
D	280 mm	Outside diameter
B	51 mm	Width, inner ring
C	39 mm	Width, outer ring
T	51 mm	Width, total
C_r	495.000 N	Basic dynamic load rating, radial
C_{0r}	930.000 N	Basic static load rating, radial
C_{ur}	109.000 N	Fatigue load limit, radial
n_G	2.320 1/min	Limiting speed
n_{gr}	1.410 1/min	Thermal speed rating
	9,486 kg	Weight

Dimensions

	T3EC200	Comparative designation to ISO 10317 and ISO 355
$r_{1,2 \text{ min}}$	3 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \text{ min}}$	2,5 mm	Minimum chamfer dimension of outer ring back face
a	54 mm	Distance between the apexes of the pressure cones
d_1	239 mm	Guidance rib diameter of inner ring

Mounting dimensions

$d_{a \max}$	216 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	212 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	257 mm	Minimum diameter of housing shoulder
$D_{a \max}$	268 mm	Maximum diameter of housing shoulder
$D_{b \min}$	271 mm	Minimum diameter of housing shoulder
$C_{a \min}$	9 mm	Minimum axial space
$C_{b \min}$	12 mm	Minimum axial space
$r_{a \max}$	3 mm	Maximum fillet radius of shaft
$r_{b \max}$	2,5 mm	Maximum fillet radius of housing

Calculation factors

e	0,39	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,52	Dynamic axial load factor
Y_0	0,84	Static axial load factor

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	200 °C	Operating temperature max.