



FAG

33012-XL

Tapered roller bearing

Schaeffler ID:
0926486730000Tapered roller bearings 330, main
dimensions to DIN ISO 355 / DIN 720,
separable, adjusted or in pairs

X-life

Technical information

**Main Dimensions & Performance Data**

d	60 mm	Bore diameter
D	95 mm	Outside diameter
B	27 mm	Width, inner ring
C	21 mm	Width, outer ring
T	27 mm	Width, total
C_r	113.000 N	Basic dynamic load rating, radial
C_{0r}	149.000 N	Basic static load rating, radial
C_{ur}	25.000 N	Fatigue load limit, radial
n_G	8.000 1/min	Limiting speed
n_{gr}	4.650 1/min	Thermal speed rating
	0,76 kg	Weight

Dimensions

	T2CE060	Comparative designation to ISO 10317 and ISO 355
$r_{1,2 \text{ min}}$	1,5 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \text{ min}}$	1,5 mm	Minimum chamfer dimension of outer ring back face
a	20 mm	Distance between the apices of the pressure cones
d_1	78,5 mm	Guidance rib diameter of inner ring

Mounting dimensions

$d_{a \max}$	67 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	67 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	85 mm	Minimum diameter of housing shoulder
$D_{a \max}$	88 mm	Maximum diameter of housing shoulder
$D_{b \min}$	90 mm	Minimum diameter of housing shoulder
$C_{a \min}$	5 mm	Minimum axial space
$C_{b \min}$	6 mm	Minimum axial space
$r_{a \max}$	1,5 mm	Maximum fillet radius of shaft
$r_{b \max}$	1,5 mm	Maximum fillet radius of housing

Calculation factors

e	0,33	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1,83	Dynamic axial load factor
Y_0	1,01	Static axial load factor

Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.