



FAG


7416-B-XL-MP

Angular contact ball bearing

Schaeffler ID:
0191190110000Angular contact ball bearing 74..-B-XL-MP,
single row, X-life, solid brass cage

X-life

Technical information

**Main Dimensions & Performance Data**

d	80 mm	Bore diameter
D	200 mm	Outside diameter
B	48 mm	Width
C_r	200.000 N	Basic dynamic load rating, radial
C_{0r}	169.000 N	Basic static load rating, radial
C_{ur}	9.900 N	Fatigue load limit, radial
n_G	5.800 1/min	Limiting speed
n_{gr}	3.600 1/min	Reference speed
	7,758 kg	Weight

Additional information

r_{min}	3 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
D_1	153,9 mm	Shoulder diameter on outer ring wide side face
d_1	129 mm	Shoulder diameter on inner ring wide side face
a	83 mm	Distance between the apexes of the pressure cones
α	40 °	Contact angle

Mounting dimensions

$d_{a min}$	96 mm	Minimum diameter of shaft shoulder
$D_{a max}$	184 mm	Maximum diameter of housing shoulder
$D_{b max}$	191 mm	Maximaler Durchmesser der Gehäuseschulter
$r_{a max}$	2,5 mm	Maximum fillet radius of shaft
$r_{a1 max}$	1 mm	Maximum fillet radius of housing

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.

