


## SL192336-TB-BR

Cylindrical roller bearing

Schaeffler ID:  
0547119080000

Cylindrical roller bearing SL1923, full compl, roller set self-retaining, single row, semi-locating bearing, 2 ribs on outer ring, 1 rib on inner ring, type SL19

### Technical information



### Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	380 mm	Outside diameter
B	126 mm	Width
$C_r$	1.940.000 N	Basic dynamic load rating, radial
$C_{0r}$	2.600.000 N	Basic static load rating, radial
$C_{ur}$	285.000 N	Fatigue load limit, radial
$n_G$	1.120 1/min	Limiting speed
$n_{gr}$	670 1/min	Reference speed
	69,1 kg	Weight

### Dimensions

$D_1$	312,9 mm	Shoulder diameter outer ring
$D_{a\ max}$	312,5 mm	Maximum diameter of housing shoulder
$d_1$	245 mm	Shoulder diameter inner ring
$d_{a\ min}$	221,5 mm	Minimum diameter shaft shoulder
$d_{c\ min}$	245 mm	Minimum shaft shoulder
F	221,6 mm	Raceway diameter inner ring
$r_{a\ max}$	4 mm	Maximum fillet radius
$r_{min}$	4 mm	Minimum chamfer dimension
s	7 mm	Axial displacement

### Temperature range

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	120 °C	Operating temperature max.