



FAG


## 30326-XL

Tapered roller bearing

Schaeffler ID:  
0935847250000Tapered roller bearings 303, main  
dimensions to DIN ISO 355 / DIN 720,  
separable, adjusted or in pairs

X-life

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	16,66 kg	Weight

## Main Dimensions &amp; Performance Data

d	130 mm	Bore diameter
D	280 mm	Outside diameter
B	58 mm	Width, inner ring
C	49 mm	Width, outer ring
T	63,75 mm	Width, total
$C_r$	710.000 N	Basic dynamic load rating, radial
$C_{0r}$	740.000 N	Basic static load rating, radial
$C_{ur}$	98.000 N	Fatigue load limit, radial
$n_G$	2.900 1/min	Limiting speed
$n_{gr}$	2.030 1/min	Thermal speed rating

## Dimensions

$r_{1,2 \min}$	5 mm	Minimum chamfer dimension of inner ring back face
$r_{3,4 \min}$	4 mm	Minimum chamfer dimension of outer ring back face
a	53 mm	Distance between the apices of the pressure cones
$d_1$	193 mm	Guidance rib diameter of inner ring

### Mounting dimensions

$d_{a \max}$	164 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	148 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	239 mm	Minimum diameter of housing shoulder
$D_{a \max}$	262 mm	Maximum diameter of housing shoulder
$D_{b \min}$	255 mm	Minimum diameter of housing shoulder
$C_{a \min}$	8 mm	Minimum axial space
$C_{b \min}$	14,5 mm	Minimum axial space
$r_{a \max}$	5 mm	Maximum fillet radius of shaft
$r_{b \max}$	4 mm	Maximum fillet radius of housing

### Calculation factors

	T2GB130	Comparative designation to ISO 10317 and ISO 355
$e$	0,35	Limiting value of $F_a/F_r$ for the applicability of diff. Values of factors X and Y
$Y$	1,73	Dynamic axial load factor
$Y_0$	0,95	Static axial load factor