

FAG

**23184-BEA-XL-K-MB1**


Spherical roller bearing

Schaeffler ID:  
0796281500000

Spherical roller bearing 231..-BEA-XL-K-MB1, symmetric 2 outer ribs with rib washer

X-life

## Technical information

**Temperature range**

$T_{min}$	-30 °C	Operating temperature min.
$T_{max}$	200 °C	Operating temperature max.
	333 kg	Weight

**Main Dimensions & Performance Data**


d	420 mm	Bore diameter
D	700 mm	Outside diameter
B	224 mm	Width
$C_r$	6.000.000 N	Basic dynamic load rating, radial
$C_{0r}$	9.600.000 N	Basic static load rating, radial
$C_{ur}$	660.000 N	Fatigue load limit, radial
$n_G$	860 1/min	Limiting speed
$n_{gr}$	455 1/min	Reference speed

**Dimensions**

$r_{min}$	6 mm	Minimum chamfer dimension
$D_1$	609,8 mm	Bore diameter outer ring
$d_s$	12,5 mm	Diameter lubrication hole
$n_s$	23,5 mm	Width of lubricating groove

**Mounting dimensions**

$d_{a min}$	446 mm	Minimum diameter shaft shoulder
$D_{a max}$	674 mm	Maximum diameter of housing shoulder
$r_{a max}$	5 mm	Maximum recess radius
$d_{a max}$	483 mm	Maximum diameter of shaft shoulder
$d_{b min}$	443 mm	Minimum cavity diameter of the sleeve
$B_{a min}$	16 mm	Minimum cavity width of the sleeve



**Additional information**

e	0,31	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H3184-HG	Adapter sleeve
Y <sub>1</sub>	2,18	Dynamic axial load factor
	AH3184G-H	Withdrawal sleeve
Y <sub>2</sub>	3,24	Dynamic axial load factor
Y <sub>0</sub>	2,13	Static axial load factor