

Linear ball bearing and housing units

KTBO20-PP-AS (Series KTBO..-PP-AS)

open design, sealed, greased, with relubrication facility;
corrosion-resistant design possible

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	20 mm	
H	42 mm	
B	60 mm	
L	104 mm	
1)	Main load direction	
A3	9 mm	
A5	30 mm	
B2	10 mm	Dimension B2 on diameter Fw
G2	M8	
G3	M6	
H2	25 mm	Tolerance: +0,015/-0,015

H6	35,5 mm	
JB	45 mm	Tolerance: +0,15/-0,15
JL	55 mm	Tolerance: +0,15/-0,15 Dimension JL and lubrication hole symmetrical with bearing length L.
K5	M6	for fixing screw to DIN 6912
K8	NIPA2	Lubrication nipple
N1	6,4 mm	
N3	11 mm	
T5	18 mm	
α	60 °	
m	0,62 kg	Mass
C	2600 N	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.
C ₀	2550 N	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.

