



FAG

★ NU236-E-XL-M1

Cylindrical roller bearing



Schaeffler ID:
0167395310000

★ Preferred product

Cylindrical roller bearing NU...-E-XL-M1,
with cage, single row, non-locating bearing,
2 ribs on outer ring, 0 ribs on inner ring
(smooth), type NU

X-life

Technical information



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	150 °C	Operating temperature max.
	18,32 kg	Weight

Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	320 mm	Outside diameter
B	52 mm	Width
C_r	730.000 N	Basic dynamic load rating, radial
C_{0r}	830.000 N	Basic static load rating, radial
C_{ur}	98.000 N	Fatigue load limit, radial
n_G	3.250 1/min	Limiting speed
n_{gr}	1.850 1/min	Reference speed

Dimensions

r_{min}	4 mm	Minimum chamfer dimension
r_{1min}	4 mm	Minimum chamfer dimension
s	4,7 mm	Axial displacement
E	289 mm	Raceway diameter outer ring
F	217 mm	Raceway diameter inner ring
D_{1min}	278,6 mm	Minimum rib diameter outer ring

Mounting dimensions

d_{amin}	197 mm	Minimum diameter shaft shoulder
d_{amax}	214 mm	Maximum diameter of shaft shoulder
d_{bmin}	221 mm	Minimum shaft shoulder
D_{amax}	303 mm	Maximum diameter of housing shoulder
r_{amax}	3 mm	Maximum recess radius
r_{a1max}	3 mm	Maximum recess radius

