

Linear ball bearing and housing units

KGSC30-PP-AS (Series KGSC..-PP-AS)

with self-aligning linear ball bearing, open design, sealed, greased, with relubrication facility

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	30 mm	
B	86 mm	
L	68 mm	
H	82 mm	
	6	Number of rows of balls
1)		Main load direction
A2	59 mm	Tolerance: +0,15/-0,15
A4	76 mm	
A5	25 mm	Tolerance: +0,01/-0,01
B2	14,3 mm	Dimension B2 on diameter Fw
G2	M16	

H2	40 mm	Tolerance: +0,008/-0,016
H4	52 mm	
H5	9 mm	
H6	55,6 mm	
JL	42 mm	Tolerance: +0,15/-0,15 Dimension JL symmetrical to bearing length L.
K5	M12	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIP5MZ	Lubrication nipple Lubrication hole symmetrical to bearing length L.
L6	52 mm	Dimension L6 symmetrical to bearing length L.
N1	13,5 mm	
N3	20 mm	
N4	10 mm	Centring for dowel hole
T5	29 mm	
α	57 °	
m	1000 g	Mass
		Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.

C_{max}	5900 N	Basic dynamic load rating
$C_{0\ max}$	6000 N	Basic static load rating



