

FAG

## ★ 11208-TVH


Self-aligning ball bearing

Schaeffler ID:  
0167001630000

Self-aligning ball bearing 112...-TVH, plastic cage

★ Preferred product

## Technical information



## Main Dimensions &amp; Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	18 mm	Width, outer ring
B <sub>i</sub>	56 mm	Width, inner ring
r <sub>min</sub>	1,1 mm	Minimum chamfer dimension
C <sub>r</sub>	19.400 N	Basic dynamic load rating, radial
C <sub>0r</sub>	6.500 N	Basic static load rating, radial
C <sub>ur</sub>	415 N	Fatigue load limit, radial
n <sub>G</sub>	10.100 1/min	Limiting speed
n <sub>gr</sub>	8.600 1/min	Reference speed
	0,736 kg	Weight

## Dimensions

D <sub>1</sub>	67,3 mm	Shoulder diameter outer ring
d <sub>1</sub>	54 mm	Shoulder diameter inner ring
b	7 mm	Width retaining slot
t	9 mm	Height retaining slot

## Mounting dimensions

D <sub>a max</sub>	73 mm	Maximum diameter of housing shoulder
r <sub>a max</sub>	1 mm	Maximaler Hohlkehlradius

## Calculation factors

e	0,22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y <sub>1</sub>	2,91	Dynamic axial load factor
Y <sub>2</sub>	4,51	Dynamic axial load factor
Y <sub>0</sub>	3,05	Static axial load factor

