

FAG



★ 2201-TVH

Self-aligning ball bearing

Schaeffler ID:
0167026200000Self-aligning ball bearing 22...-TVH, plastic
cage

★ Preferred product

Technical information



Temperature range

T_{\min}	-30 °C	Operating temperature min.
T_{\max}	120 °C	Operating temperature max.
	0,05 kg	Weight

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	32 mm	Outside diameter
B	14 mm	Width
r_{\min}	0,6 mm	Minimum chamfer dimension
C_r	9.400 N	Basic dynamic load rating, radial
C_{0r}	1.940 N	Basic static load rating, radial
C_{ur}	123 N	Fatigue load limit, radial
n_G	24.200 1/min	Limiting speed
n_{gr}	23.300 1/min	Reference speed

Dimensions

D_1	25,9 mm	Shoulder diameter outer ring
d_1	17,1 mm	Shoulder diameter inner ring

Mounting dimensions

$d_{a \min}$	16,2 mm	Minimum diameter shaft shoulder
$D_{a \max}$	27,8 mm	Maximum diameter of housing shoulder
$r_{a \max}$	0,6 mm	Maximum fillet radius

Calculation factors

e	0,53	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,2	Dynamic axial load factor
Y_2	1,86	Dynamic axial load factor
Y_0	1,26	Static axial load factor