

Linear ball bearing and housing units

KTSS12-PP-AS (Series KTSS..-PP-AS)

adjustable clearance, with self-aligning linear ball bearing, contact seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	12 mm
H	35 mm
B	43 mm
L	70 mm
	8 Number of rows of balls
1)	Main load direction
A5	21,5 mm Tolerance: +0,01/-0,01
B1	34 mm
G2	M5
H2	18 mm Tolerance: +0,008/-0,016
H4	26,6 mm

H5	5,4 mm	
H6	16,5 mm	
JB	32 mm	Tolerance: +0,15/-0,15
JL	56 mm	Tolerance: +0,15/-0,15 Dimension JL symmetrical to bearing length L.
K5	M4	for fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIP4MZ	Lubrication nipple Lubrication hole symmetrical to bearing length L.
L6	24 mm	Dimension L6 symmetrical to bearing length L.
N1	4,3 mm	
N3	8 mm	
N4	4 mm	Centring for dowel hole
T5	11 mm	
W	2,5 mm	Width across flats
m	210 g	Mass
Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.		
C _{max}	1460 N	Basic dynamic load rating

C0 max	2100 N	Basic static load rating
--------	--------	--------------------------





