
FAG
★ 2206-K-2RS-TVH-C3


Self-aligning ball bearing

 Schaeffler ID:
0384725620030

 Self-aligning ball bearing 22..-K-2RS-TVH,
tapered bore taper 1:12, seals, plastic
cage

★ Preferred product

Technical information


Temperature range

T_{\min}	-20 °C	Operating temperature min.
T_{\max}	100 °C	Operating temperature max.
	0,26 kg	Weight

Main Dimensions & Performance Data


d	30 mm	Bore diameter
D	62 mm	Outside diameter
B	20 mm	Width
r_{\min}	1 mm	Minimum chamfer dimension
C_r	15.900 N	Basic dynamic load rating, radial
C_{0r}	4.650 N	Basic static load rating, radial
C_{ur}	295 N	Fatigue load limit, radial
n_G	6.800 1/min	Limiting speed

Dimensions

D_2	53,3 mm	Caliber diameter outer ring
d_2	37,3 mm	Caliber diameter inner ring

Mounting dimensions

$d_{a \min}$	35,6 mm	Minimum diameter shaft shoulder
$d_{a \max}$	38 mm	Maximum diameter shaft shoulder
$D_{a \max}$	56,4 mm	Maximum diameter of housing shoulder
$d_{b \min}$	33 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve
$r_{a \max}$	1 mm	Maximum fillet radius



Calculation factors

e	0,25	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
	H306	Adapter sleeve
Y ₁	2,54	Dynamic axial load factor
Y ₂	3,93	Dynamic axial load factor
Y ₀	2,66	Static axial load factor