

FAG



## ★ 61888-M

Deep groove ball bearing

Schaeffler ID:  
0190027690000Deep groove ball bearing 618..-M, single  
row, solid brass cage

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	23,8 kg	Weight

## Main Dimensions &amp; Performance Data

d	440 mm	Bore diameter
D	540 mm	Outside diameter
B	46 mm	Width
$C_r$	227.000 N	Basic dynamic load rating, radial
$C_{0r}$	355.000 N	Basic static load rating, radial
$C_{ur}$	11.100 N	Fatigue load limit, radial
$n_G$	1.980 1/min	Limiting speed
$n_{gr}$	1.190 1/min	Reference speed

## Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
$D_1$	505,9 mm	Shoulder diameter outer ring
$d_1$	474,2 mm	Shoulder diameter inner ring

## Mounting dimensions

$d_{a\min}$	450,2 mm	Minimum diameter shaft shoulder
$D_{a\max}$	529,8 mm	Maximum diameter of housing shoulder
$r_{a\max}$	2,1 mm	Maximum fillet radius

## Calculation factors

$f_0$	15,9	Calculation factor
-------	------	--------------------