

FAG



## ★ 29264-E1-MB

Axial spherical roller bearing

Schaeffler ID:  
0389995010000Axial spherical roller bearing 292..-E1-MB,  
with flanging ring

★ Preferred product

## Technical information



## Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.
	31,52 kg	Weight

## Main Dimensions &amp; Performance Data

d	320 mm	Bore diameter
D	440 mm	Outside diameter
T	73 mm	Section height
$C_a$	1.410.000 N	Basic dynamic load rating, axial
$C_{0a}$	6.500.000 N	Basic static load rating, axial
$C_{ua}$	690.000 N	Fatigue load limit, axial
$n_G$	1.420 1/min	Limiting speed
$n_{gr}$	780 1/min	Reference speed

## Dimensions

$D_1$	372 mm	Bore diameter housing washer
$d_1$	415 mm	Rip diameter shaft washer
$r_{\min}$	3 mm	Minimum chamfer dimension
$T_1$	38 mm	Height of the housing washer
$T_2$	26 mm	Height of shaft washer
$T_3$	44,5 mm	Height of the shaft washer
$T_4$	69 mm	Height of shaft washer, inc. lip ring
A	172 mm	Distance of the center point

## Mounting dimensions

$d_{a \min}$	380 mm	Minimum diameter shaft shoulder
$D_{a \max}$	406 mm	Maximum diameter of housing shoulder
$D_{b \min}$	450 mm	Minimum bore diameter housing
$d_{b \max}$	336 mm	Maximum distance sleeve
$r_{a \max}$	2,5 mm	Maximum recess radius